

C1S24VS-5PFA11F2 (Primary)

C1L24VS-5PFA11F2 (Link)

The Server Technology® Smart PDU provides local LED input current monitoring, allowing IT personnel to determine safe levels of loading on a per-phase basis while installing equipment into the rack/cabinet. The power data points, along with temperature and humidity measurements (provided via optional probes), are accessible through the built-in Web and CLI interfaces as well as through SNMP. The Smart "Primary" PDU can be connected to a Smart "Link" PDU to extend the network access to the redundant or secondary power feed.

Key Features



Network Monitoring

Gain access to valuable data through connections including HTTP(S), SSH, Telnet, SNMP, (S)FTP, SMTP, Syslog, LDAP(S), RS-232 serial, and more.



Star Multi-Linking

Provides the ability to link up to four power circuits using one IP address. Primary link provides backup power to network card.



Auto-Flip Current Display

Easy-to-read LEDs display current per phase to help prevent overloads and simplify three-phase load balancing in high-density cabinets.



High Retention Locking Outlets

Receptacles have high retention and are compatible with P-Lock type power cords.




Color Identification

Choose from six colors to designate circuits for rack PDUs in the data center. Color options include Blue, Red, Green, White, Yellow, and Black.



Hot-Swap Network Card

Network access is ensured when power is lost to the primary unit with backup power provided by the primary link unit.



Temperature/Humidity Monitoring

Primary and Link units each support two external 10' (3m) T/H probes. Receive SNMP-based alerts and email notifications.



Branch Circuit Protection

This PDU meets the UL and IEC 60950-1 requirement for branch circuit protection through use of UL489 rated magnetic-hydraulic circuit breakers or UL248 fuses.



Flexible Mounting

Includes standard button mounts along with provisions for custom mounting brackets (contact Server Technology for details).

Inputs

Input Voltage (V):	415
Frequency	50/60 Hz
Input Plug:	240/415V Wye 30A IEC 60309 3P+N+G 6 Hr
Input Current (A):	30
Input Current Rated (A):	24
Input Power Capacity (kW):	17.3

Outputs

Connector	Rating
(18) x IEC 60320/C13	North American Rating: \leq 12A @240V L-N (15A Peak)
(6) x IEC 60320/C19	North American Rating: \leq 16A @240V L-N (20A Peak)

Branch Circuit Protection

(6) 20A Fuses, six (6) branch with tool-less retraction, meets UL 60950-1 requirements (Bussmann SC-20 fuses), 100 kA Interrupt Rating

Physical

Dimensions: 69.0in tall x 1.75in wide x 2.25in deep [1753mm x 45mm x 58mm]

Environmental

Operating Environment: 32°F to 122°F / 0°C to 50°C | 8%RH to 90%RH non-condensing | 6,500ft/2km elevation

Storage Environment: -40°F to 185°F / -40°C to 85°C | 8%RH to 90%RH non-condensing | 50,000ft/15km elevation

Quiescent / Unloaded Power Draw: < 10W for all configurations

Communications & Security

10/100 Mbps Ethernet (RJ-45 connector), RS-232 serial (RJ-45 connector)

Two (2) temperature/humidity sensor inputs (4P4C), Link port (RJ-12) - {also on Link PDU}

Web-browser GUI and command-line interface (CLI): HTTP/HTTPS, TLSv1.2, SSHv2, Telnet, SNMPv2c and v3 (GET, SET, Traps), IPv4 and IPv6, LDAPv3/LDAPS, TACACS+, RADIUS, FTP/SFTP

Certifications

North American:

Safety (TUV certified, cTUVus mark)

UL Std. 60950-1, 62368-1

CAN/CSA-C22.2 No. 60950-1, CAN/CSA-C22.2 No. 62368-1

EMC

FCC Part 15 Subpart B Sections 15.107 & 15.109, Class A

CAN ICES-003, Class A

Measurement Accuracy

Input Measurement Accuracy:

LED Current = \pm 10% at 0.1 amp (0.3 - 9.9 amps) and 1 amp (> 9.9 amps) resolution

GUI Current = \pm 5% at 0.01 amp resolution (above 0.25 amp)

Optional Accessories

EMTH-2-10 Combination Temperature/Humidity Probe, 10ft (3m)

EMCU-1-1C Environmental Monitor adding:

- Two (2) EMTH-2-10 temperature/humidity ports (one probe included)
- One (1) EMWS-1-1 water sensor port (probe sold separately)
- Four (4) dry contact (NO/NC) monitoring points
- One (1) 8-bit analog-to-digital converter (0 to 5VDC)




KIT-SUS-01 StartUp Stick™ for rapid configuration Mounting Brackets

- Buttons (KIT-0020) included for tool-less mounting (see diagram)
- See the Mounting Bracket Guide for further suggestions
- Custom mounting options available. Contact your local Server Technology representative

Cable Retention Devices for non-locking cords

- EZip
- Cable Sleeve

Drawings



Part Number	Description	Rating	Input Type	Output Rating	North America	Europe	China	North America	OS	Output Type	Part Number	North America / OS
CI124V/MASTER	2100/5000W 2W/1P/PE 50/60Hz 1A4	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	1P/1L c/ 1A	IE 60032 C13 / C19	1A4, 1A5, 1A6, 1A7, 1A8, 1A9, 1A10, 1A11, 1A12, 1A13, 1A14, 1A15, 1A16, 1A17, 1A18, 1A19, 1A20, 1A21, 1A22, 1A23, 1A24, 1A25, 1A26, 1A27, 1A28, 1A29, 1A30, 1A31, 1A32, 1A33, 1A34, 1A35, 1A36, 1A37, 1A38, 1A39, 1A40, 1A41, 1A42, 1A43, 1A44, 1A45, 1A46, 1A47, 1A48, 1A49, 1A50, 1A51, 1A52, 1A53, 1A54, 1A55, 1A56, 1A57, 1A58, 1A59, 1A60, 1A61, 1A62, 1A63, 1A64, 1A65, 1A66, 1A67, 1A68, 1A69, 1A70, 1A71, 1A72, 1A73, 1A74, 1A75, 1A76, 1A77, 1A78, 1A79, 1A80, 1A81, 1A82, 1A83, 1A84, 1A85, 1A86, 1A87, 1A88, 1A89, 1A90, 1A91, 1A92, 1A93, 1A94, 1A95, 1A96, 1A97, 1A98, 1A99, 1A100
CI124V/LINK	2100/5000W 2W/1P/PE 50/60Hz 1A4	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	1P/1L c/ 1A	IE 60032 C13 / C19	1A4, 1A5, 1A6, 1A7, 1A8, 1A9, 1A10, 1A11, 1A12, 1A13, 1A14, 1A15, 1A16, 1A17, 1A18, 1A19, 1A20, 1A21, 1A22, 1A23, 1A24, 1A25, 1A26, 1A27, 1A28, 1A29, 1A30, 1A31, 1A32, 1A33, 1A34, 1A35, 1A36, 1A37, 1A38, 1A39, 1A40, 1A41, 1A42, 1A43, 1A44, 1A45, 1A46, 1A47, 1A48, 1A49, 1A50, 1A51, 1A52, 1A53, 1A54, 1A55, 1A56, 1A57, 1A58, 1A59, 1A60, 1A61, 1A62, 1A63, 1A64, 1A65, 1A66, 1A67, 1A68, 1A69, 1A70, 1A71, 1A72, 1A73, 1A74, 1A75, 1A76, 1A77, 1A78, 1A79, 1A80, 1A81, 1A82, 1A83, 1A84, 1A85, 1A86, 1A87, 1A88, 1A89, 1A90, 1A91, 1A92, 1A93, 1A94, 1A95, 1A96, 1A97, 1A98, 1A99, 1A100
CI124V/METERED	2100/5000W 2W/1P/PE 50/60Hz 1A4	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	2100/5000W c/ 2A	1P/1L c/ 1A	IE 60032 C13 / C19	1A4, 1A5, 1A6, 1A7, 1A8, 1A9, 1A10, 1A11, 1A12, 1A13, 1A14, 1A15, 1A16, 1A17, 1A18, 1A19, 1A20, 1A21, 1A22, 1A23, 1A24, 1A25, 1A26, 1A27, 1A28, 1A29, 1A30, 1A31, 1A32, 1A33, 1A34, 1A35, 1A36, 1A37, 1A38, 1A39, 1A40, 1A41, 1A42, 1A43, 1A44, 1A45, 1A46, 1A47, 1A48, 1A49, 1A50, 1A51, 1A52, 1A53, 1A54, 1A55, 1A56, 1A57, 1A58, 1A59, 1A60, 1A61, 1A62, 1A63, 1A64, 1A65, 1A66, 1A67, 1A68, 1A69, 1A70, 1A71, 1A72, 1A73, 1A74, 1A75, 1A76, 1A77, 1A78, 1A79, 1A80, 1A81, 1A82, 1A83, 1A84, 1A85, 1A86, 1A87, 1A88, 1A89, 1A90, 1A91, 1A92, 1A93, 1A94, 1A95, 1A96, 1A97, 1A98, 1A99, 1A100

ISO VIEW

Additional Information

Warranty: Server Technology offers a standard 2-year limited parts & labor warranty. Extended support is available at the time of purchase. See the Support Options on the website, or contact your local Server Technology representative for more information.

Patents: Information on Server Technology patents is available on the website at: www.servertech.com/products/patents

"Global" models are typically for use in countries outside of North America. Contact your Server Technology representative for more information about which models are appropriate for your application.

Information in this document is current as of time of publishing. Contact your Server Technology representative for the most up-to-date information. This datasheet was generated on: 18-Oct-2021

Interested in learning more about how Server Technology can help you manage and distribute power in your datacenter?
Visit us online at: www.servertech.com/products/

North America Headquarters

1040 Sandhill Road
Reno, Nevada 89521
1-775-284-2000 Tel
1-800-835-1515 Toll Free
1-775-284-2065 Fax
sales@servertech.com
www.servertech.com
www.servertechblog.com

EMEA Region

4th Floor, 25-26 Lime
Street
London, EC3M 7HR
United Kingdom
+44 20 7090 1390 Tel
salesint@servertech.com

Singapore

17 Neythal Road
Singapore, 628582
Singapore
+65 6817 9017 Tel
salesint@servertech.com

India

210, Block B, Vipul Square
Sushant Lok 1
Gurgaon, Haryana 122002
India
+91 124 410 7881 Tel
+91 124 410 7880 Fax
salesint@servertech.com

**Server
Technology**[®]
A brand of  **legrand**

©2021 Server Technology, Inc. HDOT, PIPS, POPS, CDU, Sentry, Server Technology, Power Pivot, EZip, StartUp Stick and PRO2 are U.S. registered trademarks of Server Technology, Inc. All others are registered trademarks are trademarks of their respective owners. Information is subject to change without notice. Server Technology offers a wider range of products for North America and Global Markets; for more information visit www.servertech.com.