# C2W36TE-EQAF2M99 (Primary)

**C2X36TE-EQAF2M99 (Link)**

The Server Technology® PRO2 Switched PDU provides control of outlet power and local LED input current monitoring, allowing IT personnel to determine safe levels of loading on a per-phase basis while installing equipment into the rack/cabinet. The integral PIPS® technology provides billing-grade accurate measurement of current, voltage, active power, apparent power, power factor, crest factor, and accumulated energy at the input. These power data points, along with temperature and humidity measurements (provided via optional probes), are accessible through the built-in Web and CLI interfaces as well as through SNMP. The PRO2 Switched "Primary" PDU can be connected to as many as three (with optional module) PRO2 Switched "Link" PDUs to extend the network access to the redundant or secondary power feed without the risks of a daisy chain linking configuration.

## Key Features

**HDOT Cx Outlets**
Cx is the future-ready UL tested hybrid of a C13 and C19 outlet accommodating both C14 and C20 plugs.

**Hot-Swap Network Card**
Network access is ensured when power is lost to the Primary unit with backup power provided by the Linked unit.

**Temperature/Humidity Monitoring**
Primary and Expansion (select products) units each support two external 10' (3m) T/H probes. Receive SNMP-based alerts and email notifications.

**Per-Inlet Power Sensing**
PIPS® (Per Inlet Power Sensing) Monitors Current Load (A), Voltage (V), Power (W), Apparent Power (VA), Crest Factor, Power Factor, & Energy per inlet.

**Branch Circuit Protection**
This PDU meets the UL and IEC 62368-1 requirement for branch circuit protection through UL 489 rated magnetic-hydraulic circuit breakers or UL 248 fuses.

**High Temperature Rating**
This product has been tested and approved for safe and reliable operation in 60 °C data center environments.

**Color-Coded Options**
Select from six colors to designate PDU circuits in the data center — black, white, red, green, blue, and yellow.

**Network Monitoring**
Gain access to valuable data through connections including HTTP(S), SSH, Telnet, SNMP, (S)FTP, SMTP, Syslog, LDAP(S), RS-232 serial, and more.

**Star Multi-Linking**
PRO2 provides the ability to link up to four power circuits using one IP address. Primary Expansion PDU provides backup power to network card.

**Auto-Flip Current Display**
Easy-to-read LEDs display current per phase to help prevent overloads and simplify three-phase load balancing in high-density cabinets.

**Branch Current Monitoring**
Monitors current at each breaker branch and provides SNMP-based alerts and emails on high usage that risks a tripped circuit.

**Outlet Control**
On Switched PDUs, cycle power to individual outlets or groups of outlets to reboot servers, or power off unused receptacles.

**Flexible Mounting**
Includes standard button mounts along with provisions for custom mounting brackets.

## Inputs

| | |
|---|---|
| Input Voltage (V): | 230 |
| Frequency | 50/60 Hz |
| Input Plug: | IEC 230V/63A 2P+PE 6Hr |
| Input Current (A): | 63 |
| Input Current Rated (A): | 48 |
| Input Power Capacity (kW): | 11 |

## Outputs

| Connector | Rating |
|---|---|
| (18) x IEC 60320/C13 | Global Rating: ⩽ 10A @230V L-N |
| (18) x Cx | Global Rating: ⩽ 16A @230V L-N |

The Cx outlet has superior cable retention. Moderate force is required when plugging in a C14 or C20 connector to fully seat the plug and to ensure proper installation. An incorrectly installed plug will be loose and will not provide a reliable connection.

Outlet #1 opposite the power input

## Branch Circuit Protection

UL 489, CSA C22.2 No. 5 & IEC/EN 60947-2 Compliant 2-pole, 20A trip circuit breakers, three (3) branch, rating: ⩽ 16A, 10 kAIC (North America) / (5 kAIC ROW) Interrupt Rating

## Physical

Dimensions: 70.0in tall x 2.2in wide x 2.5in deep [1778mm x 56mm x 64mm]

## Environmental

**Operating Environment:** 32°F to 140°F / 0°C to 60°C | 8%RH to 90%RH non-condensing | 6,500ft/2km elevation
**Storage Environment:** -22°F to 176°F / -30°C to 80°C | 8%RH to 90%RH non-condensing | 50,000ft/15km elevation
**Quiescent / Unloaded Power Draw:** < 10W for all configurations

## Communications & Security

10/100/1000 Mbps Ethernet (RJ-45 connector), RS-232 serial (RJ-45 connector)
Two (2) temperature/humidity sensor inputs (4P4C), Link port (RJ-12) - {also on Link PDU}
Web-browser GUI and command-line interface (CLI): HTTP/HTTPS, TLSv1.2, SSHv2, Telnet, SNMPv2c and v3 (GET, SET, Traps), IPv4 and IPv6, LDAPv3/LDAPS, TACACS+, RADIUS, FTP/SFTP

## Certifications

**Global**:
Safety
  EN IEC 62368-1 (TUVR certified, T-mark)
  IEC 62368-1 incl. regional, national and harmonized differences (IECEE CB scheme) EMC
EMC
  EN 55032 / CISPR 32
  EN 55035 / CISPR 35
  EN 61000-3-2 / IEC 61000-3-2
  EN 61000-3-3 / IEC 61000-3-3

CE Mark
  2011/65/EU (RoHS Directive)
  2014/35/EU (Low Voltage Directive)
  2014/30/EU (EMC Directive)
UKCA Mark
  RoHS
  Electrical Equipment (Safety)
  Electromagnetic Compatibility

## Measurement Accuracy

**Input Measurement Accuracy:**
Input Measurement Accuracy
LED Current = ± 10% at 0.1 amp (0.5 - 9.9 amps) and 1 amp (> 9.9 amps) resolution
GUI Current = ± 1% at 0.01 amp resolution (above 0.5 amp)
Voltage = ± 1% at 0.1 volt resolution (nominal ± 10%)
Active Power = ± 1% at 1 watt resolution
Apparent Power = ± 1% at 1 volt-amp resolution
Power Factor = ± 3% at 0.01 resolution
Crest Factor = ± 10% at 0.1 resolution
Energy = ± 1% at 0.1 kilowatt-hour resolution

**Branch Measurement Accuracy**
Current = ± 3% at 0.01 amp resolution (above 0.5 amp)

## Optional Accessories

EMTH-2-10 Combination Temperature/Humidity Probe, 10ft (3m)
EMCU-1-1C Environmental Monitor adding:
- Two (2) EMTH-2-10 temperature/humidity ports (one probe included)
- One (1) EMWS-1-1 water sensor port (probe sold separately)
- Four (4) dry contact (NO/NC) monitoring points
- One (1) 8-bit analog-to-digital converter (0 to 5VDC)
KIT-PRO2LINK-01M or -01D provides ability to link (2) additional PRO2 units
KIT-SUS-01 StartUp Stick™ for rapid configurationMounting Brackets
- Buttons (KIT-0020) included for tool-less mounting (see diagram)
- See the Mounting Bracket Guide for further suggestions
- Custom mounting options available. Contact your local Server Technology representative
Cable Retention Devices for non-locking cords
- EZip
- Cable Sleeve

# Drawings


20.0 [0.79]
68.4 [2.69]
31.3 [1.23]
422.3 [16.63]
933.5 [36.75]
1555.8 [61.25]
63.9 [2.52] (SMART SWITCHED POPS HEIGHT)
72.5 [2.85] (SWITCHED POPS HEIGHT)
SEE DETAIL A
1778.0 [70.00]
SEE 412-CMA-0883 FOR ALL OUTLET CONFIGURATIONS
55.9 [2.20]
2X 77.1 [3.03]
INPUT POWER CORD ENTRY THIS END
CB
CT
PLUG
L1
L2 / NEUT
GND
A







1. DIMENSIONS ARE IN MILLIMETERS AND [ ] BRACKETS ARE IN INCHES.
2. DIMENSIONS ARE NOMINAL. INFORMATION IS SUBJECT TO CHANGE WITHOUT NOTICE.




DETAIL A
NETWORK OPTIONS




**SMART/SWITCHED VERSIONS**

(21)C13



(9)CX, (9)C13

**SMART POPS/SWITCHED POPS VERSIONS**

(6)CX, (12)C13

ISO VIEW



## Additional Information

**Warranty:** Server Technology offers a standard 2-year limited parts & labor warranty. Extended support is available at the time of purchase. See the Support Options on the website, or contact your local Server Technology representative for more information.

**Patents:** Information on Server Technology patents is available on the website at: www.servertech.com/products/patents

“Global” models are typically for use in countries outside of North America. Contact your Server Technology representative for more information about which models are appropriate for your application.

Information in this document is current as of time of publishing. Contact your Server Technology representative for the most up-to-date information. This datasheet was generated on: 17-NOV-2026

Interested in learning more about how Server Technology can help you manage and distribute power in your datacenter? Visit us online at: www.servertech.com/products/

To contact an expert in your region, go to www.servertech.com/about-us/office-locations for more information.

servertech.com ©2026 Legrand. All rights reserved. The industry-leading brands of Raritan, Server Technology, Starline, and Ortronics empower Legrand’s Data, Power & Control to deliver innovative solutions for data centers, building networks, and facility infrastructures.